# TOA PROFESSIONAL SOUND SYSTEM

# COMPRESSION DRIVER

HFD-220-8/16



# **DESCRIPTION**

The TOA HFD-220-8/16 compression driver, in 8-ohm and 16-ohm versions, is designed for use in high-level applications where sound systems of the highest quality are required. With a throat diameter of 2 in. (49mm), the TOA HFD-220-8/16 is intended for use with the TOA LE Series constant directivity horns, and it will provide highly efficient sound reproduction and a smooth frequency response from 800Hz to 15kHz. The voice coil of the TOA HFD-220-8/16 compression driver consists of a 1.76 in. (44.6mm) edgewound, copper-clad aluminum ribbon coupled to a 50micron hard duralumin diaphragm. The diaphragm voice coil assembly can be replaced in the field without having to disassemble the entire driver. The diaphragm voice coil employs self-aligning dowels to center it perfectly in the voice coil gap. The gap has a flux density of 19,000 gauss, generated by a 2.4 lbs. (1.1 kg) ferrite magnet. A machined phasing plug with two acoustic slots serves as the pole piece, providing the proper phase relationship between the sound emanating from the center and that coming from the edge of the diaphragm/voice coil assembly.

### **FEATURES**

- 1. Smooth frequency response from 800Hz to 15kHz.
- 2. Highly efficient sound pressure level of 110dB/W/m with LE-940 horn.
- 3. High power capacity: 30 watts continuous pink noise (800Hz to 20kHz, test duration: 24 hours).
- 4. Throat diameter of 2 in. (49mm).
- 5. Edge-wound, copper-clad aluminum ribbon voice coil.
- 6. 50-micron duralumin diaphragm.
- Diaphragm voice coil can be easily replaced in the field.



# **SPECIFICATIONS**

Power Handling Capacity				
Continuous Pink Noise	30 watts RMS band-limited pink noise			
	(800Hz to 20kHz)			
Continuous Program	90 watts			
Nominal Impedance	8 ohms (HFD-220-8)			
	16 ohms (HFD-220-16)			
Frequency Response	800Hz to 15kHz			
Pressure Sensitivity	110dB/W/m: LE-940 horn			
800Hz to 5kHz pink noise	112dB/W/m: LE-640 horn			
4-meter measurement	114dB/W/m: LE-420 horn			
distance referred to	108dB/W/m: LE-M124 horn			
1 meter	10SdB/W/m: LE-M94 horn			
	112dB/W/m: LE-M64 horn			
	114dB/W/m: LE-M42 horn			
Recommended Crossover	800Hz or higher			
Frequency				
Throat Diameter	2" (49mm)			
Polarity	Positive voltage to +terminal produces			
•	negative acoustic pressure in the throat			
Recommended Horn	LE-940, LE-640, LE-420			
	LE-M124, LE-M94, LE-M64, LE-M42			
Magnet	2.4 lbs. (1.1 kg) Ferrite			
	Flux density: 19,000 gauss			
Diaphragm	Heat-treated 50-micron duralumin			
Voice Coil	1.76" (44.6mm) dia., edge-wound			
	copper-clad aluminum ribbon			
Finish	Black NEW-ALKONE paint			
Dimensions	5.98" (152mm) dia.			
	7.01" (178mm) depth			
Net Weight	10.6 lbs. (4.8kg)			
Mounting Data	Four studs [0.24" (6mm) dia.] equally			
<u>-</u>	spaced on a 4" (101.6mm) dia. circle			
·				

#### Notes:


- 1. Measurement conditions:
- The above electrical and acoustic data are measured in conjunction with TOA's LE-M94 horn.

  2. Duration of power handling test is 24 hours.
- \*Specifications are subject to change without notice.

# ARCHITECT'S AND ENGINEER'S SPECIFICATIONS

The compression driver shall be the TOA HFD-220-8/16, in 8-ohm or 16ohm versions, or an approved equivalent. Power handling capacity shall be 90 watts of continuous program, 30 watts RMS band-limited pink noise (800Hz to 20kHz), with a smooth frequency response from 800Hz to 15kHz. Pressure sensitivity with the LE-940 horn shall be 110dB/Wm,when measured at a referred 1 -meter distance on an axis from the mouth of the LE-940 with 1-watt input pink noise, band limited from 800Hz to 5kHz, and the recommended crossover frequency shall be 800Hz or higher. Nominal impedance shall be 8 ohms for the HFD-220-8 and 16 ohms for the HFD-220-16. The unit's throat diameter shall be 2 in. (49mm). The voice coil shall consist of a 1.76in. (44.6mm) edge-wound, copper-clad aluminum ribbon coupled to a 50-micron hard duralumin diaphragm. The diaphragm voice coil assembly shall be replaceable in the field without requiring special tools or skills. The diaphragm voice coil shall employ self-aligning dowels to center it perfectly in the voice coil gap. The gap shall have a flux density of 19,000 gauss generated by a 2.4 lbs. (1.1 kg) ferrite magnet. A machined phasing plug with three acoustic slots shall serve as the pole piece, providing the proper phase relationship between the sound emanating from the center and that coming from the edge of the diaphragm/voice coil assembly. The driver shall be 598 in. (152mm) in diameter by 7.01 in. (178mm) in depth, shall weigh 10.6 lbs. (4.8kg), and shall have a black NEW-ALKONE paint finish. Mounting shall be effected by four 6mm studs, equally spaced on a 4in. (101.6mm) diameter circle.

# APPEARANCE AND DIMENSIONAL DIAGRAM




# **EQUALIZATION**


When using the HFD-220-8/16 driver in combination with the LE Series constant directivity horn and the TOA "SAORI" integrated sound processor, set the long delay type horn equalizer (IS-110DL4, IS-110DL2) built into the digital channel divider module of the "SAORI" as shown in the table below.

1		LE-940	LE-640	LE-420	LE-M124	LE-M94	LE-M64	LE-M42
	HFD-220-8/16	TYPE 6	TYPE 6	TYPE 7	TYPE 8	TYPE 8	TYPE 8	TYPE 9


# CHARACTERISTIC DIAGRAMS


• Frequency Response and Impedance







- \*4-meter measurement distance referred to 1 meter, 1W, sine wave.
- Harmonic Distortion





- \*4-meter measurement distance referred to 1 meter, 1W, sine wave
- Frequency Response with Horn EQ





\*4-meter measurement distance referred to 1 meter, 1W, sine wave, with Horn EQ Type 6 (LE-940), Type 8 (LE-M94)



**TOA**Electronics, Inc., 601 Gateway Boulevard South San Francisco, California 94080

Telephone: (415) 588-2538 FAX (415) 588-3349